



YSR44FX31LTCKITC, Compression Splice Reducer, Barrel A 750 kcmil, Barrel B 350 kcmil, includes clear heat shrink

By Burndy
Catalog # [YSR44FX31LTCKITC](#)

CU Splice Reducer, Barrel A 750 kcmil G,H,777 DLO, Barrel B 350 kcmil CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	750 KCMIL-300 KCMIL
Conductor - Copper Flex K Size A	750 KCMIL
Conductor - Copper Flex K Size A Range	750 KCMIL
Conductor - Copper Flex M Size A Range	750 KCMIL
Conductor - Copper Flex M Run	750 KCMIL
Conductor - Copper Flex M Size A	750 KCMIL
Conductor - Copper Str Size	750 KCMIL-300 KCMIL
Conductor - Copper Flex K Run	750 KCMIL
Conductor - Copper Flex G Size A	750 kcmil
Conductor - Copper Flex G Size A Range	750 kcmil
Conductor - Copper Flex G Run	750 KCMIL
Conductor - Copper Str Size A	750 kcmil



Conductor - Copper Flex H Run	750 KCMIL
Conductor Size	750 KCMIL-300 KCMIL
Conductor - Copper Str Size B	350 kcmil
Conductor - Copper Flex H Size A	750 kcmil
Conductor - Copper Str Size A Range	750 kcmil
Conductor Type	FLEX
Conductor - Copper Flex I Run	750 KCMIL
Conductor - Copper Str Size B Range	350 kcmil
Conductor - Copper Flex H Size A Range	750 kcmil
Conductor - Copper Flex I Size A	750 KCMIL
Conductor - Copper Flex I Size A Range	750 KCMIL

Configuration

Connector Type	STANDARD BARREL KITS
----------------	----------------------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	132 mm
Dimension - Strip Length inch	1.96 in
Dimension - B Length fraction	2-1/16 in
Dimension - B Length inch	2.09 in
Dimension - Length BB inch	1.49 in
Dimension - Length Overall	5.18 in
inch	

General

Trade Name	HYREDUCER™
Die Index	L115/18
Die Index - Element A	L115
Die Index - Element B	18

Die Index Run Side	L115
Die Index Tap Side	18
Feature - Barrel Type	Standard
Feature - Barrel Style	Skived
Plated	Y
Color Code	Yellow, Red
UPC	781810344354
Color Code - Side B	Red
Color Code - Side A	Yellow
Material	Copper
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810344354

UPC 14 Digit GTIN00781810344354

Logistics

Minimum Pack Quantity	6
Pallet Quantity	540
Carton Quantity	6

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[French, English\]](#)



A Hubbell brand