



YSR44FX38FXLTCKITC, Compression Splice Reducer, Barrel A 750 kcmil, Barrel B 500 kcmil, includes clear heat shrink

By Burndy
Catalog # YSR44FX38FXLTCKITC

CU Splice Reducer, Barrel A 750 kcmil G,H,777 DLO, Barrel B 500 kcmil H,I,K / 550 kcmil G,H,I,535 DLO CU, Kit includes clear heat shrink

Features

- Each splice kit includes one YSR-TC compression in-line splice reducer connector and heat shrink
- Designed configurations allow for copper code-to-code wire connections, copper code-to-flex wire connections, and copper flex-to-flex wire connections
- Barrel is designed with a taper to accommodate a main run wire that is reduced to a smaller tap wire
- Electro-tin plated unless otherwise specified to reduce galvanic corrosion (bimetallic) and resist corrosive elements
- Connectors clearly marked with color coding

Application

Wire Reducing Splice

Specifications

Certification - UL Recognized	No
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Material	COPPER
Wire Size	750 KCMIL-500 KCMIL-550 KCMIL
Conductor - Copper Flex K Size B Range	500 kcmil
Conductor - Copper Flex K Tap	500-550 KCMIL
Conductor - Copper Flex K Size A	750 KCMIL
Conductor - Copper Flex K Size B	500 kcmil
Conductor - Copper Flex K Size A Range	750 KCMIL
Conductor - Copper Flex M Size B	500 kcmil
Conductor - Copper Flex M Size A Range	750 KCMIL
Conductor - Copper Flex M Size B Range	500 kcmil



Conductor - Copper Flex M Run	750 KCMIL
Conductor - Copper Flex M Size A	750 KCMIL
Conductor - Copper Str Size	750 KCMIL-500 KCMIL-550 KCMIL
Conductor - Copper Flex I Tap	500-550 KCMIL
Conductor - Copper Flex K Run	750 KCMIL
Conductor - Copper Flex I Size B	500 kcmil
Conductor - Copper Flex I Size B Range	500 kcmil
Conductor - Copper Flex G Size A	750 kcmil
Conductor - Copper Flex G Size B	500 kcmil
Conductor - Copper Flex G Size A Range	750 kcmil
Conductor - Copper Flex G Run	750 KCMIL
Conductor - Copper Str Size A	750 kcmil
Conductor - Copper Flex H Run	750 KCMIL
Conductor Size	750 KCMIL-500 KCMIL-550 KCMIL
Conductor - Copper Str Size B	500 kcmil
Conductor - Copper Flex H Size A	750 kcmil
Conductor - Copper Str Size A Range	750 kcmil
Conductor - Copper Flex G Size B Range	500 kcmil
Conductor - Copper Flex G Tap	500-550 KCMIL
Conductor - Copper Flex M Tap	500-550 KCMIL
Conductor Type	FLEX
Conductor - Copper Flex H Tap	500-550 KCMIL
Conductor - Copper Flex I Run	750 KCMIL
Conductor - Copper Flex H Size B	350 kcmil
Conductor - Copper Str Size B Range	500 kcmil
Conductor - Copper Flex H Size A Range	750 kcmil
Conductor - Copper Flex H Size B Range	500 kcmil
Conductor - Copper Flex I Size A	750 KCMIL

Conductor - Copper Flex I Size 750 KCMIL
A Range

Configuration

Connector Type STANDARD BARREL KITS

Current

Voltage Rating 35 kV
Voltage - Maximum 35000

Dimensions

Package Height 0.000 in
Package Weight 0.000 lb.
Package Length 0.000 in
Package Width 0.000 in
Dimension - L Length Overall 117 mm
mm
Dimension - Strip Length inch 1.96 in
Dimension - B Length fraction 2-1/16 in
Dimension - B Length inch 2.09 in
Dimension - Length BB inch 1.60 in
Dimension - Length Overall 4.61 in
inch

General

Trade Name HYREDUCER™
Die Index L115/L99

Die Index - Element A L115
Die Index - Element B L99
Die Index Run Side L115
Die Index Tap Side L99
Feature - Barrel Type Standard
Feature - Barrel Style Skived
Plated Y
Color Code Yellow, Pink
UPC 781810472279
Color Code - Side B Pink
Color Code - Side A Yellow
Material Copper
Plating Type Tin - Electro Plated
Finish Type Tin-Plated
UPC 12 Digit 781810472279
UPC 14 Digit GTIN 00781810472279

Logistics

Minimum Pack Quantity 1
Pallet Quantity 864
Carton Quantity 6

Operational

Temperature Rating 194

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[French, English\]](#)

