



YST1C1CT, Compresson T-Connector, 1 Str Cu, Standard Barrel, Tapered Ends

By Burndy
Catalog # [YST1C1CT](#)



Cu Comprsn T- Connector, #1 STR (.330), 3.75" L, Green, 11 Index

Application

T-Connector

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
UL Listed	Yes
Certification - CSA Approved	No

Conductor

Conductor Size	1 AWG-1 AWG
Conductor - Copper Str Run Range	1 AWG
Conductor - Copper Str Run	1 AWG
Conductor - Material	COPPER
Conductor Type	CODE
Conductor - Copper Str Tap Range	1 AWG
Conductor - Copper Str Tap	1 AWG

Configuration

Connector Type	T-COUPLER
----------------	-----------

Current

Voltage Rating	35 kV
Voltage - Maximum	35000

Dimensions

Package Height	0.000 in
Dimension - Height mm	0 mm
Dimension - B Length fraction	1-3/8 in
Package Weight	0.000 lb.
Dimension - Width inch	1.61 in

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	95 mm
Dimension - B Length inch	1.38 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Inside Diameter inch	0.36 in
Dimension - Length BB inch	1.38 in
Dimension - Length Overall inch	3.75 in

General

Feature - Barrel Type	Long
Feature - Barrel Style	Tapered
Plated	Y
Trade Name	HYTEE™
Die Index	11/11
Die Index Run Side	11
UPC	781810198490
Color Code - Side B	Green
Die Index Tap Side	11
Color Code - Side A	Green
Material	COPPER
Plating Type	Tin - Electro Plated
Finish Type	Tin-Plated
UPC 12 Digit	781810198490
UPC 14 Digit GTIN	00781810198490

Logistics

Pallet Quantity	11600
Carton Quantity	25

Operational

Temperature Rating	194
--------------------	-----

Product Assets

[Catalog \[English\]](#)