



YSU25A25A, Aluminum LINKIT Splice

By Burndy
Catalog # [YSU25A25A](#)

Al(Uninsulated) Compression LINKIT Splice, 1/0 Str., 1/0 Compr,
1/0 Compt Al(Brrl A), 1/0 Str., 1/0 Compr, 1/0 Compt Al(Brrl AA)



Features

- Aluminum Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size A	1/0 AWG
Conductor - AL Str Size B	1/0 AWG

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	51 mm
mm	
Dimension - B Length inch	0.87 in
Dimension - Outside Diameter	0.65 in
inch	

Dimension - Length Overall 2 in
inch

General

Plated	Y
Trade Name	LINKIT™
Die Index	243 - BG or 5/8
UPC	781810124659
Color Code - Side B	Yellow
Color Code - Side A	Yellow
Type	Service Entrance, Uninsulated, Center Stop
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810124659
UPC 14 Digit GTIN	00781810124659

Logistics

Minimum Pack Quantity	5000
Pallet Quantity	29600
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)