

YSU25R2W, Heavy-Walled Aluminum Tube with Solid Barrier

By Burndy

Catalog # [YSU25R2W](#)



Heavy-walled AL tubing with solid barrier minimizes galvanic corrosion, Color Code: Yellow (Side A), Orange (Side B)

Features

- Heavy-walled aluminum tube with solid barrier minimizes galvanic corrosion of conductors
- Accommodates neutral strands of SE Service Entrance Conductors as well as others
- Installed with standard tooling, color-coded, and pre-filled with PENETROX Joint Compound and Stripsealed

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Str Size A	1/0 AWG
Conductor - Copper Str Size B	3 AWG, 4 AWG
Conductor - Copper Solid Size B	2 AWG
Conductor - AL Str Size A	1/0 AWG
Conductor - AL Str Size B	3 AWG, 4 AWG
Conductor - AL Str Size B Range	3 AWG-4 AWG
Conductor - ACSR Str Size A	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size B	• 4 (6/1) Swan AWG • 4 (7/1) Swanate AWG
Conductor - Copper Str Size B Range	3 AWG-4 AWG
Conductor - ACSR Str Size B Range	4 (6/1) Swan AWG-4 (7/1) Swanate AWG

Dimensions

Dimension - L Length Overall	51 mm
Dimension - B Length inch	0.87 in
Dimension - Outside Diameter inch	0.65 in
Dimension - Length Overall inch	2 in

General

Plated	Y
Trade Name	LINKIT™
Die Index	• 243 • BG or 5/8
UPC	781810143391
Color Code - Side B	Orange
Color Code - Side A	Yellow
Type	Service Entrance, Uninsulated, Center Stop
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Tin - Hot Dipped
UPC 12 Digit	781810143391
UPC 14 Digit GTIN	00781810143391

Logistics

Minimum Pack Quantity	100
Pallet Quantity	29600
Carton Quantity	100

Product Assets

[Catalog \[English\]](#)