



YSV1014G2, Reducing Splice For 12 - 10 AWG and 20 - 14 AWG

By Burndy
Catalog # [YSV1014G2](#)

Uninsulated Reducing Splice. 12-10 AWG and 20-14 AWG, Pure Electrolytic Copper, Tin Plated, Positive Wire Stops



Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating provides durable long lasting resistance to corrosion
- Positive center wire stops for proper dept of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion

Application

For Splicing Two Different Size Wires

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Flex K Size B Range	20-14
Conductor - Copper Flex K Size A	10
Conductor - Copper Flex K Size B	• 20 • 18 • 16 • 14
Conductor - Copper Flex K Size A Range	10
Conductor - Copper Flex M Size B	• 20 • 18 • 16 • 14
Conductor - Copper Flex M Size A Range	10
Conductor - Copper Flex M Size B Range	20-14
Conductor - Copper Flex M Size A	10
Conductor - Copper Str Size	• 20

	• 18 • 16 • 14 • 12 • 10
Conductor - Copper Flex I Size B	• 20 • 18 • 16 • 14
Conductor - Copper Flex I Size B Range	20-14
Conductor - Copper Flex G Size A	10
Conductor - Copper Flex G Size B	• 20 • 18 • 16 • 14
Conductor - Copper Flex G Size A Range	10
Conductor Size	20 - 14 AWG
Conductor - Copper Flex H Size A	10
Conductor - Copper Flex G Size B Range	20-14
Conductor Type	• CU C Str-Size • CU C Solid-Size • CU C Str Aircraft-Size
Conductor - Copper Flex H Size B	• 20 • 18 • 16 • 14
Conductor - Copper Str Size Range	20 AWG - 10 AWG
Conductor - Copper Flex H Size A Range	10
Conductor - Copper Flex H Size B Range	20-14
Conductor - Copper Flex I Size A	10
Conductor - Copper Flex I Size A Range	10

Configuration

Connector Type	Reducer
----------------	---------

Current

Voltage - Maximum	35000 V
-------------------	---------

Dimensions

Package Height	0.000 in
----------------	----------

Package Weight	0.000 lb.	Plated	Yes
Package Length	0.000 in	Sub Brand	HYREDUCER
Package Width	0.000 in	Product Type	Splice Reducer
Dimension - L Length Overall mm	20 mm	UPC	781810026403
Dimension - A Outside Diameter inch	0.21 in	Type	Splice
Dimension - B Length fraction	5/16 in	Material	Copper
Dimension - B Length inch	0.31 in	Plating Type	Tin
Dimension - B Outside Diameter inch	0.16 in	UPC 12 Digit	781810026403
Dimension - Length BB inch	0.27 in	UPC 14 Digit GTIN	00781810026403
Dimension - Length Overall inch	0.77 in		
General		Logistics	
Product Family	COMPRESSION	Minimum Pack Quantity	500
Trade Name	HYREDUCER™	Carton Quantity	500
Feature - Barrel Style	Chamfered		

Product Family	COMPRESSION
Trade Name	HYREDUCER™
Feature - Barrel Style	Chamfered

Product Assets

[Catalog \[English\]](#)

