



YSV10BOX, Uninsulated Splice For 12 - 10
AWG

By Burndy
Catalog # [YSV10BOX](#)

Uninsulated Splice, 12-10 AWG, Seamless Tubing - No Seams to Split,
Tin Plated Electrolytic Copper, Positive Wire Stops

Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating provides durable long lasting resistance to corrosion
- Positive center wire stops for proper dept of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion

Application

For All Heavy Duty Industrial And General Purpose Applications

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor - Copper Str Size	12-10 AWG
Conductor Size	12 - 10 AWG
Conductor - Copper Solid Size	12-10 AWG
Conductor - Copper Str Aircraft Size	• AN 12 • AN 10
Conductor Type	• CU C Str-Size • CU C Solid-Size • CU C Str Aircraft-Size

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Current

Voltage - Maximum	35000 V
-------------------	---------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	19 mm
Dimension - Outside Diameter inch	0.21 in
Dimension - Strip Length inch	5/16 in
Dimension - Length Overall inch	0.75 in

General

Product Family	COMPRESSION
Trade Name	HYLINK™
Feature - Barrel Style	Chamfered
Plated	Yes
Sub Brand	HYLINK
Product Type	Splice
UPC	781810543603
Type	Splice
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810543603

Logistics

Minimum Pack Quantity	50
Pallet Quantity	99999
Carton Quantity	600

Product Assets

[Catalog \[English\]](#)