



YSV10NK, Uninsulated Splice For 12 - 10 AWG (Nickel Plated)

By Burndy

Catalog # [YSV10NK](#)

Uninsulated Splice For 12 - 10 AWG (Nickel Plated)



Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plated provides durable long lasting resistance to corrosion
- Positive center wire stops for proper depth of wire insertion
- Marked with wire size providing easy wire size indentification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion
- Nickel plated for high temperature applications up to 650°F continuous service and 750°F intermittent service

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Solid Size	• 12 • 11 • 10
Conductor - Copper Solid Size Range	12-10
Conductor - Copper Str Aircraft Size	• AN 12 • AN 10
Conductor - Copper Str Aircraft Size Range	AN 12-AN 10
Conductor - Copper Str Navy Size	• 6 (7) • 6 (19) • 9 (7) • 9 (37)
Conductor - Copper Str Navy Size Range	6 (7)-9 (37)
Conductor Size	12 - 10 AWG
Conductor - Copper Str Size	• 12 • 10
Conductor - Copper Str Size Range	12 AWG - 10 AWG
Conductor Type	• CU C Str-Size

- CU C Solid-Size
- CU C Str Aircraft-Size

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Current

Voltage - Maximum	35000 V
-------------------	---------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	5/16 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.31 in
Dimension - Outside Diameter inch	0.21 in
Dimension - L Length Overall mm	19 mm
Package Height	0.000 in
Dimension - Inside Diameter inch	0.13 in
Dimension - Strip Length inch	5/16
Dimension - Length Overall inch	0.75 in

General

Die Index	36
Trade Name	HYLINK™
Plated	Y
Feature - Barrel Style	Chamfered
Type	Splice
UPC 12 Digit	781810162781
UPC 14 Digit GTIN	00781810162781
Material	Copper
Plating Type	Nickel
UPC	781810162781

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99999

Product Assets

[Catalog \[English\]](#)



A Hubbell brand