



YSV1214G1, Reducing Splice For 12 AWG and 16 - 14 AWG

By Burndy
Catalog # [YSV1214G1](#)

Uninsulated Reducing Splice, 12 AWG and 16-14 AWG, Seamless Tubing, Tin Plated Copper

Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating provides durable long lasting resistance to corrosion
- Positive center wire stops for proper dept of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion

Application

For Splicing Two Different Size Wires

Specifications

Certification - UL Recognized	No
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Copper Flex K Size B Range	20-14
Conductor - Copper Flex K Size B	• 20 • 18 • 16 • 14
Conductor - Copper Flex M Size B	• 20 • 18 • 16 • 14
Conductor - Copper Flex M Size B Range	20-14
Conductor - Copper Str Size	• 16 • 14 • 12
Conductor - Copper Flex I Size B	• 20 • 18 • 16



Conductor - Copper Flex I Size B Range	• 14 20-14
Conductor - Copper Flex G Size B	• 20 • 18 • 16 • 14
Conductor Size	16 - 14 AWG
Conductor - Copper Flex G Size B Range	20-14
Conductor Type	• CU C Str-Size • CU C Solid-Size • CU C Str Aircraft-Size
Conductor - Copper Flex H Size B	• 20 • 18 • 16 • 14
Conductor - Copper Str Size Range	16 AWG - 12 AWG
Conductor - Copper Flex H Size B Range	20-14

Configuration

Connector Type	Reducer
----------------	---------

Current

Voltage - Maximum	35000 V
-------------------	---------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	21 mm
Dimension - A Outside Diameter inch	0.18 in
Dimension - B Length fraction	5/16 in
Dimension - B Length inch	0.29 in
Dimension - B Outside Diameter inch	0.16 in
Dimension - Length BB inch	0.26 in
Dimension - Length Overall inch	0.81 in

General

Product Family	COMPRESSION
Trade Name	HYREDUCER™

Feature - Barrel Style	Chamfered	UPC 14 Digit GTIN	00781810026410
Plated	Yes	Logistics	
Sub Brand	HYREDUCER	Minimum Pack Quantity	500
Product Type	Splice Reducer	Carton Quantity	500
UPC	781810026410	Product Assets	
Type	Splice	Catalog [English]	
Material	Copper		
Plating Type	Tin		
UPC 12 Digit	781810026410		

