



# YSV14HBOX, Uninsulated Splice For 16 - 14 AWG

By Burndy  
Catalog # [YSV14HBOX](#)

Uninsulated Splice with Cable Strain Relief, 16-14 AWG, Seamless Butt Splice, Electrolytic Copper Tubing, Tin Plated, Positive Wire Stops

## Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating provides durable long lasting resistance to corrosion
- Positive center wire stops for proper dept of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion

## Application

For All Heavy Duty Industrial And General Purpose Applications

## Specifications

|                                    |                      |
|------------------------------------|----------------------|
| Certification - UL Recognized      | No                   |
| Buy American Compliant             | Contact Manufacturer |
| Certification - cULus              | No                   |
| Buy America(n) Qualified           | Contact Manufacturer |
| Certification - ETL                | No                   |
| Standards - Industry Standards Met | UL486                |
| Standards - RoHS Compliance        | CM                   |
| Status                             |                      |
| UL Listed                          | Yes                  |
| Certification - CSA Approved       | Yes                  |

## Conductor

|                                      |                                                                                                                                                 |
|--------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------|
| Conductor - Copper Str Size          | <ul style="list-style-type: none"><li>• 22</li><li>• 20</li><li>• 18</li><li>• 16</li><li>• 14</li></ul>                                        |
| Conductor Size                       | 16 - 14 AWG                                                                                                                                     |
| Conductor - Copper Solid Size        | <ul style="list-style-type: none"><li>• 20</li><li>• 18</li><li>• 17</li><li>• 16</li><li>• 15</li><li>• 14</li><li>• 13</li><li>• 12</li></ul> |
| Conductor - Copper Str Aircraft Size | <ul style="list-style-type: none"><li>• AN 20</li><li>• AN 18</li><li>• AN 16</li></ul>                                                         |



## Conductor Type

- AN 14
- AN 12
- CU C Str-Size
- CU C Solid-Size
- CU C Str Aircraft-Size

## Configuration

|                |                      |
|----------------|----------------------|
| Connector Type | Seamless Butt Splice |
|----------------|----------------------|

## Current

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 600 V |
|-------------------|-------|

## Dimensions

|                                    |           |
|------------------------------------|-----------|
| Package Height                     | 0.000 in  |
| Package Weight                     | 0.000 lb. |
| Package Length                     | 0.000 in  |
| Package Width                      | 0.000 in  |
| Dimension - L Length Overall mm    | 24 mm     |
| Dimension - Outside Diameter inch  | 0.16 in   |
| Dimension - Strip Length inch      | 1/4 in    |
| Dimension - Diameter Max Size inch | 0.15 in   |
| Dimension - Length Overall inch    | 0.94 in   |
| Cable Insulation Diameter Maximum  | 0.150 in  |

## General

|                        |                |
|------------------------|----------------|
| Product Family         | COMPRESSION    |
| Trade Name             | HYLINK™        |
| Feature - Barrel Style | Chamfered      |
| Plated                 | Yes            |
| Sub Brand              | HYLINK         |
| Product Type           | Splice         |
| UPC                    | 781810534502   |
| Type                   | Splice         |
| Material               | Copper         |
| Plating Type           | Tin            |
| UPC 14 Digit GTIN      | 00781810534502 |

## Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 100   |
| Pallet Quantity       | 99999 |
| Carton Quantity       | 1200  |



A Hubbell brand