



YSV14NK, Uninsulated Splice For 16 - 14 AWG (Nickel Plated)

By Burndy
Catalog # YSV14NK

Uninsulated Splice For 16 - 14 AWG (Nickel Plated)

Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plated provides durable long lasting resistance to corrosion
- Positive center wire stops for proper depth of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion
- Nickel plated for high temperature applications up to 650°F continuous service and 750°F intermittent service

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - RoHS Compliance	CM
Status	
Certification - CSA Approved	No
UL Listed	No

Conductor

Conductor - Copper Solid Size	12
Conductor - Copper Str Aircraft Size	• AN 20 • AN 18 • AN 16 • AN 14
Conductor - Copper Str Navy Size	• 2 1/2 (1) • 2 1/2 (19) • 2 1/2 (26) • 3 (7) • 4 (1) • 4 (7) • 4 (19) • 4 (41)
Conductor Size	16 - 14 AWG
Conductor - Copper Str Size	• 20 • 18 • 16 • 14
Conductor Type	• CU C Str-Size

- CU C Solid-Size
- CU C Str Aircraft-Size

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Current

Voltage - Maximum	35000 V
-------------------	---------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	1/4 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.25 in
Dimension - Outside Diameter inch	0.16 in
Dimension - L Length Overall mm	16 mm
Package Height	0.000 in
Dimension - Strip Length inch	1/4 in
Dimension - Length Overall inch	0.64 in

General

Die Index	36
Trade Name	HYLINK™
Plated	Y
Feature - Barrel Style	• Chamfered • Shrouded
Type	Splice
UPC 14 Digit GTIN	00781810080894
Material	Copper
Plating Type	Nickel
UPC	781810080894

Logistics

Minimum Pack Quantity	200
Carton Quantity	200

Product Assets

[Catalog \[English\]](#)

