



YSV18H, Uninsulated Splice For 22 - 18 AWG

By Burndy
Catalog # [YSV18H](#)

Uninsulated Splice For 22 - 18 AWG



Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating provides durable long lasting resistance to corrosion
- Positive center wire stops for proper dept of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion

Specifications

Certification - cULus	No
Certification - UL Recognized	No
Certification - ETL	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
Certification - CSA Approved	Yes
UL Listed	Yes

Conductor

Conductor - Copper Solid Size	• 20 • 18
Conductor - Copper Solid Size Range	20-18
Conductor - Copper Str Aircraft Size	• AN 22 • AN 20 • AN 18
Conductor - Copper Str Aircraft Size Range	AN 22-AN 18
Conductor - Copper Str Navy Size	• 1 (1) • 1 (7) • 1 (10) • 1 1/2 (1) • 1 1/2 (7) • 1 1/2 (16) • 1 1/2 (41) • 2 (7) • 2 1/2 (1) • 2 1/2 (19) • 2 1/2 (26)

Conductor - Copper Str Navy Size Range	1 (1)-2 1/2 (26)
Conductor Size	22 - 18 AWG
Conductor - Copper Str Size	• 22 • 20 • 18
Conductor - Copper Str Size Range	22 AWG - 18 AWG
Conductor Type	• CU C Str-Size • CU C Solid-Size • CU C Str Aircraft-Size

Configuration

Connector Type	Seamless Butt Splice
----------------	----------------------

Current

Voltage - Maximum	35000 V
-------------------	---------

Dimensions

Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length fraction	1/4 in
Package Weight	0.000 lb.
Dimension - B Length inch	0.22 in
Dimension - Outside Diameter inch	0.12 in
Dimension - L Length Overall mm	23 mm
Package Height	0.000 in
Dimension - Inside Diameter inch	0.06 in
Dimension - Strip Length inch	1/4
Dimension - Length Overall inch	0.89 in

General

Trade Name	HYLINK™
Plated	Y
Feature - Barrel Style	Shrouded
Type	Splice
UPC 12 Digit	781810805725
UPC 14 Digit GTIN	00781810805725
Material	Copper
Plating Type	Tin
UPC	781810805725

Logistics

Minimum Pack Quantity	1000
Carton Quantity	1000
Pallet Quantity	99000

Operational

Temperature Rating	90
--------------------	----

Product Assets

[Catalog \[English\]](#)



A Hubbell brand