



YSV1CLFX, Compression Splice, #1 AWG Cu Flex

By Burndy
Catalog # [YSV1CLFX](#)

1 Flex G,H,I,K,M,DLO, 1 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Green Color Code, 11 Die Index.

Features

- Standard Barrel
- Internal Chamfer
- Tin Plated

Application

Wire Splice

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer NO
EU RoHS Indicator	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper Flex G Size	1 AWG
Conductor - Copper DLO Size	1 AWG
Range	
Conductor - Copper DLO Size	1 AWG
Conductor Size	1 AWG
Conductor - Copper Flex H Size	1 AWG
Conductor - Copper Flex G Size	1 AWG
Range	
Conductor - Material	COPPER
Wire Size	1 AWG
Conductor - Copper Flex K Size	1 AWG
Range	
Conductor - Copper Flex K Size	1 AWG
Conductor - Copper Flex M Size	1 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	1 AWG

Conductor - Copper Flex H Size	1 AWG
Range	
Conductor - Copper Flex I Size	1 AWG
Conductor - Copper Flex I Size	1 AWG
Range	

Configuration

Connector Type	STANDARD BARREL
----------------	-----------------

Current

Voltage Rating	35 kV
----------------	-------

Dimensions

Length	2.07 in
Dimension - B Length inch	0.84

General

Color Code	Green
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	11
UPC	621945623927
Type	YSV
Construction Material - Main	Copper
Material	COPPER
Finish Type	Tin-Plated

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[French, English\]](#)