



YSV29LFX Compression Splice, 250 kcmil, 4/0 Flex Cu

By Burndy
Catalog # [YSV29LFX](#)

250 KCMIL B,C, 4/0 Flex G,H,I,K,M,DLO, 4/0 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Yellow Color Code, 16 Die Index.

Features

- Standard Barrel
- Internal Chamfer
- Tin Plated
- UL Listed, CSA Certified

Application

Wire Splice

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer NO
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified Industry Standard(s)	Contact Manufacturer UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper Flex G Size	4/0 AWG
Conductor - Copper DLO Size	4/0 AWG
Range	
Conductor - Copper DLO Size	4/0 AWG
Conductor Size	250 KCMIL
Conductor - Copper Flex H Size	4/0 AWG
Conductor - Copper Flex G Size	4/0 AWG
Range	
Conductor - Material	COPPER
Wire Size	4/0 AWG
Conductor - Copper Flex K Size	4/0 AWG
Range	
Conductor - Copper Flex K Size	4/0 AWG
Conductor - Copper Flex M Size	4/0 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	4/0 AWG



Conductor - Copper Flex H Size	4/0 AWG
Range	
Conductor - Copper Flex I Size	4/0 AWG
Conductor - Copper Flex I Size	4/0 AWG
Range	

Configuration

Connector Type	STANDARD BARREL
----------------	-----------------

Current

Voltage Rating	35 kV
----------------	-------

Dimensions

Length	2.17 in
Dimension - B Length inch	0.89

General

Color Code	Yellow
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	16
UPC	621945623972
Type	YSV
Construction Material - Main Material	Copper
Material	COPPER
Finish Type	Tin-Plated

Logistics

Pallet Quantity	9600
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[French, English\]](#)