



YSV2CFX, Compression Splice, #2 AWG Cu Flex

By Burndy
Catalog # [YSV2CFX](#)

2 Flex G,H,I,K,M,DLO, 2 AWG CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Brown Color Code, 10 Die Index.

Features

- Long Barrel
- Internal Chamfer
- Tin Plated
- UL Listed, CSA Certified

Application

Wire Splice

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer NO
EU RoHS Indicator	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper Flex G Size	2 AWG
Conductor - Copper DLO Size	2 AWG
Range	
Conductor - Copper DLO Size	2 AWG
Conductor Size	2 AWG
Conductor - Copper Flex H Size	2 AWG
Conductor - Copper Flex G Size	2 AWG
Range	
Conductor - Material	COPPER
Wire Size	2 AWG
Conductor - Copper Flex K Size	2 AWG
Range	
Conductor - Copper Flex K Size	2 AWG
Conductor - Copper Flex M Size	2 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	2 AWG



Conductor - Copper Flex H Size	2 AWG
Range	
Conductor - Copper Flex I Size	2 AWG
Conductor - Copper Flex I Size	2 AWG
Range	

Configuration

Connector Type	LONG BARREL
----------------	-------------

Current

Voltage Rating	35 kV
----------------	-------

Dimensions

Length	3.06 in
Dimension - B Length inch	1.34

General

Color Code	Brown
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	10
UPC	621945624061
Type	YSV
Construction Material - Main Material	Copper COPPER
Finish Type	Tin-Plated

Logistics

Carton Quantity	20
-----------------	----

Product Assets

- [Catalog \[English\]](#)
[Installation Manual \[French, English\]](#)