



YSV3CFX, Compression Splice, #3 Flex Cu

By Burndy
Catalog # [YSV3CFX](#)

3 Flex G,H,I,K,M,DLO, 3 AWG CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, White Color Code, 9 Die Index.



Features

- Long Barrel
- Internal Chamfer
- Tin Plated
- UL Listed, CSA Certified

Application

Wire Splice

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer NO
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	Contact Manufacturer
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper Flex G Size	3 AWG
Conductor - Copper DLO Size	3 AWG
Range	
Conductor - Copper DLO Size	3 AWG
Conductor Size	3 AWG
Conductor - Copper Flex H Size	3 AWG
Conductor - Copper Flex G Size	3 AWG
Range	
Conductor - Copper Solid Size	2 Sol
Range	
Conductor - Material	COPPER
Wire Size	3 AWG
Conductor - Copper Flex K Size	3 AWG
Range	
Conductor - Copper Flex K Size	3 AWG
Conductor - Copper Flex M Size	3 AWG
Conductor Type	CODE/FLEX

Conductor - Copper Str Size	3 AWG
Conductor - Copper Flex H Size	3 AWG
Range	
Conductor - Copper Flex I Size	3 AWG
Conductor - Copper Flex I Size	3 AWG
Range	

Configuration

Connector Type	LONG BARREL
----------------	-------------

Current

Voltage Rating	35 kV
----------------	-------

Dimensions

Length	2.81 in
Dimension - B Length inch	1.21

General

Color Code	White
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	9
UPC	621945624054
Type	YSV
Construction Material - Main	Copper
Material	COPPER
Finish Type	Tin-Plated

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[French, English\]](#)