



YSV4CFX, Compression Splice, #4 Flex Cu

By Burndy
Catalog # [YSV4CFX](#)

4 Flex G,H,I,K,M,DLO, 4 AWG CU, Long Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Gray Color Code, 8 Die Index.



Features

- Long Barrel
- Internal Chamfer
- Tin Plated
- UL Listed, CSA Certified

Application

Wire Splice

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer NO
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified	BABA Compliant (All status valid till December 2026)
Industry Standard(s)	UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper Flex G Size	4 AWG
Conductor - Copper DLO Size	4 AWG
Range	
Conductor - Copper DLO Size	4 AWG
Conductor Size	4 AWG
Conductor - Copper Flex H Size	4 AWG
Conductor - Copper Flex G Size	4 AWG
Range	
Conductor - Material	COPPER
Wire Size	4 AWG
Conductor - Copper Flex K Size	4 AWG
Range	
Conductor - Copper Flex K Size	4 AWG
Conductor - Copper Flex M Size	4 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	4 AWG
Conductor - Copper Flex H Size	4 AWG
Range	

Conductor - Copper Flex I Size	4 AWG
Conductor - Copper Flex I Size	4 AWG
Range	

Configuration

Connector Type	LONG BARREL
----------------	-------------

Current

Voltage Rating	35 kV
----------------	-------

Dimensions

Package Height	0.000 in
Length	2.79 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - B Length inch	1.21

General

Color Code	Gray
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	8
UPC	621945624047
Type	YSV
Construction Material - Main Material	Copper
Finish Type	COPPER
	Tin-Plated

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[French, English\]](#)