



YSV4CLFX, Compression Splice, #4 AWG Flex Cu

By Burndy
Catalog # [YSV4CLFX](#)

4 Flex G,H,I,K,M,DLO, 4 AWG CU, Standard Barrel, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, Gray Color Code, 8 Die Index.

Features

- Standard Barrel
- Internal Chamfer
- Tin Plated
- UL Listed, CSA Certified

Application

Wire Splice

Specifications

Buy American Compliant Certification - cULus	Contact Manufacturer NO
EU RoHS Indicator	Contact Manufacturer
Buy America(n) Qualified Industry Standard(s)	Contact Manufacturer UL 486A-486B
Certification - CSA Approved	CSA

Conductor

Conductor - Copper Flex G Size	4 AWG
Conductor - Copper DLO Size	4 AWG
Range	
Conductor - Copper DLO Size	4 AWG
Conductor Size	4 AWG
Conductor - Copper Flex H Size	4 AWG
Conductor - Copper Flex G Size	4 AWG
Range	
Conductor - Material	COPPER
Wire Size	4 AWG
Conductor - Copper Flex K Size	4 AWG
Range	
Conductor - Copper Flex K Size	4 AWG
Conductor - Copper Flex M Size	4 AWG
Conductor Type	CODE/FLEX
Conductor - Copper Str Size	4 AWG



Conductor - Copper Flex H Size	4 AWG
Range	
Conductor - Copper Flex I Size	4 AWG
Conductor - Copper Flex I Size	4 AWG
Range	

Configuration

Connector Type	STANDARD BARREL
----------------	-----------------

Current

Voltage Rating	35 kV
----------------	-------

Dimensions

Length	2.04 in
Dimension - B Length inch	0.84

General

Color Code	Gray
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	8
UPC	621945623859
Type	YSV
Construction Material - Main Material	Copper COPPER
Finish Type	Tin-Plated

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalog \[English\]](#)
[Installation Manual \[French, English\]](#)