



# YSV6CFXBNK, Uninsulated Splice For 6 AWG (Nickel Plated)

By Burndy  
Catalog # [YSV6CFXBNK](#)

Uninsulated Splice For 6 AWG (Nickel Plated)



## Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plated provides durable long lasting resistance to corrosion
- Positive center wire stops for proper depth of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion
- Nickel plated for high temperature applications up to 650°F continuous service and 750°F intermittent service

## Specifications

|                                    |       |
|------------------------------------|-------|
| Certification - cULus              | No    |
| Certification - UL Recognized      | No    |
| Certification - ETL                | No    |
| Standards - Industry Standards Met | UL486 |
| Standards - RoHS Compliance Status | CM    |
| Certification - CSA Approved       | Yes   |
| UL Listed                          | Yes   |

## Conductor

|                                  |                                                                                           |
|----------------------------------|-------------------------------------------------------------------------------------------|
| Conductor - Copper Solid Size    | 6 AWG                                                                                     |
| Conductor - Copper Str           | 6                                                                                         |
| Compact Size                     |                                                                                           |
| Conductor - Copper DLO Size      | 6 (61/#24) DLO                                                                            |
| Conductor - Copper Flex G Size   | 6 AWG                                                                                     |
| Conductor - Copper Str Navy Size | 30 (19)                                                                                   |
| Conductor - Copper Flex H Size   | 6 AWG                                                                                     |
| Conductor - Copper Str Size      | 6 AWG                                                                                     |
| Conductor Type                   | <ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul> |
| Conductor - Copper Flex I Size   | 6 AWG                                                                                     |
| Conductor - Copper Flex K Size   | 6 AWG                                                                                     |
| Conductor - Copper Flex M Size   | 6 AWG                                                                                     |

## Configuration

|                |        |
|----------------|--------|
| Connector Type | Splice |
|----------------|--------|

## Dimensions

|                                   |           |
|-----------------------------------|-----------|
| Package Length                    | 0.000 in  |
| Package Width                     | 0.000 in  |
| Dimension - B Length fraction     | 1-3/16 in |
| Package Weight                    | 0.000 lb. |
| Dimension - B Length inch         | 1.22 in   |
| Dimension - Outside Diameter inch | 0.31 in   |
| Dimension - L Length Overall mm   | 67 mm     |
| Package Height                    | 0.000 in  |
| Dimension - Strip Length inch     | 1-5/16 in |
| Dimension - Length Overall inch   | 2.62 in   |
| Dimension - D inch                | 0.37 in   |

## General

|                        |                |
|------------------------|----------------|
| Die Index              | 7              |
| Color Code             | Blue           |
| Trade Name             | HYLINK™        |
| Plated                 | Y              |
| Feature - Barrel Type  | Long           |
| Feature - Barrel Style | Belled         |
| Type                   | Splice         |
| UPC 14 Digit GTIN      | 00781810195949 |
| Material               | Copper         |
| Plating Type           | Nickel         |
| UPC                    | 781810195949   |

## Logistics

|                       |    |
|-----------------------|----|
| Minimum Pack Quantity | 50 |
| Carton Quantity       | 50 |

## Product Assets

[Catalog \[English\]](#)