



YSV9CL, Uninsulated Splice, 9 AWG, Seamless

By Burndy
Catalog # [YSV9CL](#)

Uninsulated Butt Splice, 9 AWG, Seamless, Electrolytic copper, Tin Plated, Wire Stop for Proper Depth of Wire Insertion

Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating provides durable long lasting resistance to corrosion
- Positive center wire stops for proper dept of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion

Application

For Aircraft, Light Duty Industrial And General Purpose Applications

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance	CM
Status	
Buy American Compliant	Contact Manufacturer
Certification - cULus	No
Buy America(n) Qualified	Contact Manufacturer
UL Listed	Yes
Certification - CSA Approved	Yes

Conductor

Conductor Size	9 AWG
Conductor - Copper Solid Size	9
Conductor - Copper Str Aircraft Size	AN 9
Conductor Type	• CU C Str-Size • CU C Solid-Size • CU C Str Aircraft-Size
Conductor - Copper Str Size	9

Configuration



Connector Type Seamless Butt Splice

Current

Voltage - Maximum 600 V

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	5/16 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall mm	19 mm
Dimension - B Length inch	0.31 in
Dimension - Outside Diameter inch	0.23 in
Dimension - Length Overall inch	0.75 in
Dimension - Strip Length inch	5/16

General

Feature - Barrel Style	• Chamfered • Shrouded
Plated	Yes
Product Family	COMPRESSION
Trade Name	HYLINK™
Sub Brand	HYLINK
Die Index	92
Product Type	Splice
UPC	781810805749
Type	Splice
Material	Copper
Plating Type	Tin
UPC 14 Digit GTIN	00781810805749

Logistics

Minimum Pack Quantity	200
Carton Quantity	200

Product Assets

[Catalog \[English\]](#)