



# YSV9CLBOX, Uninsulated Splice For 9 AWG

By Burndy  
Catalog # [YSV9CLBOX](#)

Uninsulated Splice For 9 AWG

## Features

- Manufactured from seamless tubing
- High quality design with no seams to split
- Electrolytic copper provides maximum conductivity, low resistance and ductility for excellent crimp forming properties
- Electro-tin plating provides durable long lasting resistance to corrosion
- Positive center wire stops for proper dept of wire insertion
- Marked with wire size providing easy wire size identification
- HYLINK splice connectors feature inspection holes providing easy visual inspection of proper wire insertion

## Application

For Aircraft, Light Duty Industrial And General Purpose Applications

## Specifications

|                                    |                      |
|------------------------------------|----------------------|
| Buy American Compliant             | Contact Manufacturer |
| Certification - cULus              | No                   |
| EU RoHS Indicator                  | Yes                  |
| Certification - UL Recognized      | No                   |
| Buy America(n) Qualified           | Contact Manufacturer |
| Certification - ETL                | No                   |
| Standards - Industry Standards Met | UL486                |
| Standards - RoHS Compliance Status | CM                   |
| Certification - CSA Approved       | Yes                  |
| UL Listed                          | Yes                  |

## Conductor

|                                            |                 |
|--------------------------------------------|-----------------|
| Conductor - Copper Str Size                | 9               |
| Conductor - Copper Solid Size              | 9               |
| Conductor - Copper Solid Size Range        |                 |
| Conductor - Copper Str Aircraft Size       | AN 9            |
| Conductor - Copper Str Aircraft Size Range |                 |
| Conductor Size                             | 9 AWG           |
| Conductor - Copper Str Size Range          | 9 AWG           |
| Conductor Type                             | • CU C Str-Size |

- CU C Solid-Size
- CU C Str Aircraft-Size

## Configuration

|                |                      |
|----------------|----------------------|
| Connector Type | Seamless Butt Splice |
|----------------|----------------------|

## Current

|                   |       |
|-------------------|-------|
| Voltage - Maximum | 600 V |
|-------------------|-------|

## Dimensions

|                                   |         |
|-----------------------------------|---------|
| Dimension - Outside Diameter inch | 0.23 in |
| Dimension - L Length Overall mm   | 19 mm   |
| Dimension - Strip Length inch     | 5/16 in |
| Dimension - B Length fraction     | 1/3 in  |
| Dimension - B Length inch         | 0.31 in |
| Dimension - Length Overall inch   | 0.75 in |

## General

|                        |                      |
|------------------------|----------------------|
| Trade Name             | HYLINK™              |
| Sub Brand              | HYLINK               |
| Plated                 | Y                    |
| Feature - Barrel Style | Chamfered            |
| Type                   | Splice               |
| UPC 12 Digit           | 781810534304         |
| UPC 14 Digit GTIN      | 00781810534304       |
| Material               | Copper               |
| Plating Type           | Tin - Electro Plated |
| UPC                    | 781810534304         |

## Logistics

|                       |       |
|-----------------------|-------|
| Minimum Pack Quantity | 50    |
| Carton Quantity       | 600   |
| Pallet Quantity       | 99999 |

## Operational

|                    |    |
|--------------------|----|
| Temperature Rating | 90 |
|--------------------|----|

## Product Assets

[Catalog \[English\]](#)



A Hubbell brand