



YTS312E, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS312E](#)



Al Full Tension Splice For Extra High Steel Guy, Messenger or "Static" Cable,5/16 EHS Steel

Features

- ACSR Full Tension Compression Splice
- For Extra High Steel Guy, Messenger or Static Cable

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Grade	EHS
Conductor - Galvanized Steel	5/16 (7) in
Str Size	

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	287 mm
mm	
Dimension - Length Overall	11.30 in
inch	

General

Trade Name	HYSPLICE™
Die Index	721
UPC	781810107010
Material	Aluminum Alloy
UPC 12 Digit	781810107010
UPC 14 Digit GTIN	00781810107010

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3600
Carton Quantity	40

Product Assets

[Catalog \[English\]](#)