



YTS32R, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS32R](#)

Aluminum outer sleeve for full tension splice kit, 336.4 Kcmil, 717 Index, Outer sleeve for Hysplices provides gradual transition of stress



Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	336 kcmil
Conductor - AL Str Size Range	336 kcmil
Conductor - ACSR Str Size	• 336.4 (24/7) Widgeon Kcmil • 336.4 (26/7) Linnet Kcmil • 336.4 (30/7) Oriole Kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	439.4 mm
Dimension - Length Overall	17.30 inch

General

Trade Name	HYSPLICE™
Die Index	717
UPC	781810000526
Material	Aluminum
UPC 12 Digit	781810000526
UPC 14 Digit GTIN	00781810000526

Logistics

Minimum Pack Quantity	1
Pallet Quantity	768
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)