



YTS32R34RS, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS32R34RS](#)



Full Tension Splice Kit for ACSR Conductor

Features

- ACSR Full Tension Compression Splice Kit

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	336.4 (26/7) Linnet kcmil
Conductor - ACSR Str Size Range	336.4 (26/7) Linnet Kcmil, 336.4 (24/7) Widgeon Kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	439 mm
Dimension - Outside Diameter	1.19 in
Dimension - Length Overall	17.30 in

General

Trade Name	HYSPLICE™
UPC	781810221570
Material	Aluminum
UPC 12 Digit	781810221570
UPC 14 Digit GTIN	00781810221570

Logistics

Minimum Pack Quantity	1
Pallet Quantity	576
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)