



YTS331A, ACSR - Full Tension Compression Splice



By Burndy
Catalog # [YTS331A](#)

Al Tube Full Tensiion Splice, 450, 477 kcmil Al, 230 kV, 9.27" L,
719 Index

Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 450 (37) Cosmos Kcmil • 477 (19) Cosmos Kcmil • 477 (37) Syringa Kcmil
Conductor - AL Str Size Range	450 kcmil-477 kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	235 mm
Dimension - Length Overall	9.27 in

General

Plated	N
Trade Name	HYSPLICE™
Die Index	719
UPC	781810016206
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810016206
UPC 14 Digit GTIN	00781810016206

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2520
Carton Quantity	15

Product Assets

[Catalog \[English\]](#)