



YTS34R, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS34R](#)



Aluminum outer sleeve for full tension splice kit, 397.5 Kcmil, 719 Index, Outer sleeve for Hysplices provides gradual transition of stress

Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	397 kcmil
Conductor - AL Str Size Range	397 kcmil
Conductor - ACSR Str Size	397.5 (26/7) Ibis kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	438 mm
Dimension - Length Overall	17.25 in

General

Trade Name	HYSPLICE™
Die Index	719
UPC	781810000519
Material	Aluminum
UPC 12 Digit	781810000519
UPC 14 Digit GTIN	00781810000519

Logistics

Minimum Pack Quantity	1
Pallet Quantity	768
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)