



YTS34RS, ACSR - Full Tension Compression Splice



By Burndy
Catalog # [YTS34RS](#)

Steel Sleeve, 336.4, 397.5 kcmilACSR, 230 V, 5.74" L, 718 Index,
Included in Full Tension Splice

Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 336 kcmil • 350 kcmil • 397 kcmil
Conductor - AL Str Size Range	336 kcmil-397 kcmil
Conductor - ACSR Str Size	• 336.4 (24/7) Widgeon Kcmil • 336.4 (26/7) Linnet Kcmil • 397.5 (26/7) Ibis Kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	145.8
mm	
Dimension - B Length inch	2.45
Dimension - Length Overall	5.74
inch	

General

Trade Name	HYSPLICE™
Die Index	718
UPC	781810016213
Material	Steel
UPC 12 Digit	781810016213
UPC 14 Digit GTIN	00781810016213

Logistics

Minimum Pack Quantity	1
Pallet Quantity	4350
Carton Quantity	25

Product Assets

[Catalog \[English\]](#)