



YTS351AT, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS351AT](#)



Full Tension Splice for Stranded Aluminum Transmission Line

Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 500 (37) Hyacinth Kcmil • 556.5 (19) Dahlia Kcmil • 556.5 (37) Mistletoe Kcmil
-------------------------	--

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - B Length fraction	5-13/16 in
-------------------------------	------------

Dimension - L Length Overall	302 mm
Dimension - B Length inch	5.82 in
Dimension - Outside Diameter	1.41 in
Dimension - Length Overall	11.88 in

General

Trade Name	HYSPLICE™
Die Index	720
UPC	781810515457
Material	Aluminum
UPC 12 Digit	781810515457
UPC 14 Digit GTIN	00781810515457

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2016
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)