



YTS361A, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS361A](#)

Aluminum full tension HYSPLICE™, 600-636 Kcmil, 722 Index



Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 600 kcmil • 636 kcmil
Conductor - AL Str Size Range	600 kcmil-636 kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	308 mm
	mm
Dimension - Length Overall	12.14 in
	inch

General

Trade Name	HYSPLICE™
Die Index	722
UPC	781810129203
Material	Aluminum
UPC 12 Digit	781810129203
UPC 14 Digit GTIN	00781810129203

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1512
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)