



YTS36R, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS36R](#)

Aluminum outer sleeve for full tension splice kit, 477 Kcmil, 720 Index, Outer sleeve for Hysplices provides gradual transition of stress



Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	477 kcmil
Conductor - AL Str Size Range	477 kcmil
Conductor - ACSR Str Size	• 477.0 (24/7) Flicker kcmil • 477.0 (26/7) Hawk kcmil
Conductor - ACSR Str Size Range	477.0 (24/7) Flicker kcmil-477.0 (26/7) Hawk kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	461.3 mm
Dimension - Length Overall	18.16 inch

General

Trade Name	HYSPLICE™
Die Index	720
UPC	781810081617
Material	Aluminum
UPC 12 Digit	781810081617
UPC 14 Digit GTIN	00781810081617

Logistics

Minimum Pack Quantity	1
Pallet Quantity	768
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)