



YTS375E, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS375E](#)



Full tension aluminum splice for EHS steel guy, messenger or "static" cable. ANSI C119.4 Class 1 (Full Tension),10-3/8 L

Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	RUS
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Grade	EHS
Conductor - Galvanized Steel Str Size	3/8 (7) in
Conductor - Galvanized Steel Str Size Range	3/8 (7) in

Configuration

Connector Type	Splice
Dimensions	
Dimension - L Length Overall mm	264 mm
Dimension - Length Overall inch	10.40
General	
Trade Name	HYSPLICE™
Die Index	723
UPC	781810016152
Material	Aluminum Alloy
UPC 12 Digit	781810016152
UPC 14 Digit GTIN	00781810016152

Logistics

Minimum Pack Quantity	1
Pallet Quantity	3360
Carton Quantity	40

Product Assets

[Catalog \[English\]](#)