



YTS391A, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS391A](#)

Al Tube Full Tension Splice, 795 kcmil Al, 37 Str,795 kcmil Al, 61 Str, 800 kcmil Al, 61 Str, 15.81" L, For Stranded Al Cable

Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 795 (37, 61) Kcmil • 800 (61) Kcmil
-------------------------	---

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall mm	402 mm
---------------------------------	--------



Dimension - Length Overall inch	15.81 in
General	
Plated	N
Trade Name	HYSPLICE™
Die Index	724
UPC	781810016220
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810016220
UPC 14 Digit GTIN	00781810016220

Logistics

Minimum Pack Quantity	1
Pallet Quantity	960
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)