



YTS391AT, ACSR - Full Tension Compression Splice



By Burndy
Catalog # [YTS391AT](#)

Al Tube Full Tension Splice, EHV, 795 - 800 kcmil Al, 16.36" L, 724
Index

Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 795 kcmil • 800 kcmil
Conductor - AL Str Size Range	795 kcmil-800 kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	416 mm
Dimension - Outside Diameter	1.61 inch
Dimension - Length Overall	16.36 in

General

Trade Name	HYSPLICE™
Die Index	724
UPC	781810016244
Material	Aluminum
UPC 12 Digit	781810016244
UPC 14 Digit GTIN	00781810016244

Logistics

Minimum Pack Quantity	1
Pallet Quantity	960
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)