



YTS39A, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS39A](#)

Al Tube Full Tension Splice, 715.5, 750 kcmil Al, 230 kV, 13.36" L, 724 Index



Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 715.5 (37, 61) Kcmil • 750 (61) Kcmil
-------------------------	---

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	339 mm
------------------------------	--------

Dimension - Length Overall	13.36 in
inch	
General	
Plated	N
Trade Name	HYSPLICE™
Die Index	724
UPC	781810016169
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810016169
UPC 14 Digit GTIN	00781810016169

Logistics

Minimum Pack Quantity	1
Pallet Quantity	900
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)