



YTS39AR, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS39AR](#)



Al Tubing Full Tension Splice, 634.9, 649.5, 653.1 kcmil ACAR,
16.38" L, 722 Index

Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size	634.9 Kcmil, 649.5 Kcmil, 653.1 Kcmil
---------------------------	---------------------------------------

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	416 mm
Dimension - Length Overall	16.39 in

General

Trade Name	HYSPLICE™
Die Index	722
UPC	781810016145
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810016145
UPC 14 Digit GTIN	00781810016145

Logistics

Minimum Pack Quantity	1
Pallet Quantity	1152
Carton Quantity	12

Product Assets

[Catalog \[English\]](#)