



YTS39R, Aluminum Outer Sleeve for Full Tension Splice Kit

By Burndy
Catalog # [YTS39R](#)



Aluminum outer sleeve for full tension splice kit, 556.5 Kcmil, 722 Index, Outer sleeve for HYSPLICE™ provides gradual transition of stress

Features

- Aluminum Outer Sleeve For Full Tension Splice Kit

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	556.5 (24/7) Parakeet kcmil 556.5 (26/7) Dove kcmil
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet kcmil-556.5 (26/7) Dove kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall mm	505 mm
Dimension - Length Overall inch	19.875 in

General

Trade Name	HYSPLICE™
Die Index	722
UPC	781810000533
Material	Aluminum
UPC 12 Digit	781810000533
UPC 14 Digit GTIN	00781810000533

Logistics

Minimum Pack Quantity	1
Pallet Quantity	768
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)