



YTS39R43RS, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS39R43RS](#)



Full Tension Splice Kit for ACSR Conductor

Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	• 556.5 (24/7) Parakeet kcmil • 556.5 (26/7) Dove kcmil
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet kcmil-556.5 (26/7) Dove kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.

Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	505 mm
Dimension - B Length inch	2.47 in
Dimension - Outside Diameter inch	1.50 in
Dimension - Length Overall inch	19.88 in

General

Trade Name	HYSPLICE™
UPC	781810209462
Material	Aluminum
UPC 12 Digit	781810209462
UPC 14 Digit GTIN	00781810209462

Logistics

Minimum Pack Quantity	1
Pallet Quantity	480
Carton Quantity	5

Product Assets

[Catalog \[English\]](#)