



YTS39RT43RS, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS39RT43RS](#)



Full Tension Splice Kit for ACSR Conductor EHV

Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	• 556.5 (24/7) Parakeet kcmil • 556.5 (26/7) Dove kcmil
Conductor - ACSR Str Size Range	556.5 (24/7) Parakeet kcmil-556.5 (26/7) Dove kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Dimension - B Length fraction	2-1/2 in

Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	527 mm
Dimension - Outside Diameter	1.50 inch
Dimension - Length Overall	20.74 in

General

Trade Name	HYSPLICE™
UPC	781810515532
Material	Aluminum
UPC 12 Digit	781810515532
UPC 14 Digit GTIN	00781810515532

Logistics

Minimum Pack Quantity	1
Pallet Quantity	144
Carton Quantity	2

Product Assets

[Catalog \[English\]](#)