



YTS431A, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS431A](#)

Al Tube Full Tension Splice, 874.5, 954 kcmil Al, 230 kV, 16.51" L, 725 Index



Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 874.5 (37, 61) Kcmil • 954 (37, 61) Kcmil
-------------------------	---

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	419 mm
------------------------------	--------

Dimension - Length Overall	16.51 in
----------------------------	----------

General

Plated	N
Trade Name	HYSPLICE™
Die Index	725
UPC	781810016312
Prefilled Oxide Inhibitor	Y
Material	Aluminum
Plating Type	Unplated
UPC 12 Digit	781810016312
UPC 14 Digit GTIN	00781810016312

Logistics

Minimum Pack Quantity	1
Pallet Quantity	768
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)