



YTS431AT, Aluminum Full Tension Splice

By Burndy
Catalog # [YTS431AT](#)

Al Full Tension Splice For Stranded Aluminum Transmission Line, 874.5 kcmil, 954 kcmil, 345 kV, 725 Index, Extra High Voltage Applications



Features

- Aluminum Compression Full Tension Splice
- Extra High Voltage Applications

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	874.5 (37, 61) Kcmil - 954 (37, 61) Kcmil
Conductor - AL Str Size Range	874.5 Kcmil-954 Kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	455 mm
Dimension - Length Overall	17.92 in

General

Trade Name	HYSPLICE™
Die Index	725
UPC	781810055298
Material	Aluminum
UPC 12 Digit	781810055298
UPC 14 Digit GTIN	00781810055298

Logistics

Minimum Pack Quantity	8
Pallet Quantity	768
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)