



YTS438E, ACSR - Full Tension Compression Splice



By Burndy
Catalog # [YTS438E](#)

Full tension aluminum splice for EHS steel guy, messenger or "static" cable. ANSI C119.4 Class 1 (Full Tension), 12.32" L

Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - Industry Standards Met	RUS
Standards - RoHS Compliance Status	CM
Certification - cULus	No
Industry Standard(s)	RUS
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - Galvanized Steel Str Size	7/16 (7) in
---------------------------------------	-------------

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	313 mm
Dimension - Length Overall	12.32 in

General

Trade Name	HYSPLICE™
Die Index	726
UPC	781810016190
Material	Aluminum Alloy
UPC 12 Digit	781810016190
UPC 14 Digit GTIN	00781810016190

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2520
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)