



YTS43R, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS43R](#)



Aluminum outer sleeve for full tension splice kit, 605-666.6 Kcmil, 724 Index, Outer sleeve for Hysplices provides gradual transition of stress

Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	• 605 (24/7) Peacock Kcmil • 605 (26/7) Squab Kcmil • 605 (30/19) Teal Kcmil • 636 (24/7) Rook Kcmil • 636 (26/7) Grosbeak Kcmil • 636 (30/19) Egret Kcmil • 666.6 (24/7) Flamingo Kcmil • 666.6 (54/7) Gull Kcmil
Conductor - ACSR Str Size Range	605 (24/7) Peacock Kcmil - 666.6 (54/7) Gull Kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall mm	545 mm
Dimension - Length Overall inch	21.4375 in

General

Trade Name	HYSPLICE™
Die Index	724
UPC	781810091456
Material	Aluminum
UPC 12 Digit	781810091456
UPC 14 Digit GTIN	00781810091456

Logistics

Minimum Pack Quantity	9
Pallet Quantity	648
Carton Quantity	9

Product Assets

[Catalog \[English\]](#)