



YTS43R43RS, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS43R43RS](#)



Full Tension Splice Kit for ACSR Conductor

Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	• 605 (24/7) Peacock kcmil • 605 (26/7) Squab kcmil • 605 (30/19) Teal kcmil • 636 (24/7) Rook kcmil • 636 (26/7) Grosbeak kcmil • 636 (30/19) Egret kcmil • 666.6 (24/7) Flamingo kcmil
Conductor - ACSR Str Size Range	605 (24/7) Peacock kcmil-666.6 (24/7) Flamingo kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	545 mm
Dimension - Outside Diameter	1.61 in
Dimension - Length Overall	21.44 in

General

Trade Name	HYSPLICE™
UPC	781810211137
Material	Aluminum
UPC 12 Digit	781810211137
UPC 14 Digit GTIN	00781810211137

Logistics

Minimum Pack Quantity	8
Pallet Quantity	144
Carton Quantity	2

Product Assets

[Catalog \[English\]](#)