

YTS43RS, Steel Sleeve

By Burndy
Catalog # [YTS43RS](#)



Steel Sleeve, 605, 363, 666.6 kcmil ACSR, 230 V, 5.90" L, 723 Index, Included in Full Tension Splice

Features

- Steel Sleeve

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	556 kcmil 600 kcmil 636 kcmil 650 kcmil
Conductor - AL Str Size Range	556 kcmil-650 kcmil
Conductor - ACSR Str Size	556.5 (24/7) Parakeet Kcmil 556.5 (26/7) Dove Kcmil 605 (24/7) Peacock Kcmil 605 (26/7) Squab Kcmil 605 (30/19) Teal Kcmil 636 (24/7) Rook Kcmil 636 (26/7) Grosbeak Kcmil

Conductor - ACSR Str Size Range

- 636 (30/19) Egret Kcmil
- 666.6 (24/7) Flamingo Kcmil
- 666.6 (54/7) Gull Kcmil
- 556.5 (24/7) Parakeet Kcmil - 666.6 (54/7) Gull Kcmil

Configuration

Connector Type	Splice
----------------	--------

General

Trade Name	HYSPLICE™
Die Index	723
UPC	781810016251
Material	Aluminum
UPC 12 Digit	781810016251
UPC 14 Digit GTIN	00781810016251

Logistics

Minimum Pack Quantity	1
Pallet Quantity	2320
Carton Quantity	20

Product Assets

[Catalog \[English\]](#)