



YTS445A, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS445A](#)

Aluminum Full Tension HYSPLICE™, 1033.5-1113 Kcmil, 727 Index



Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	1033.5 (37, 61) Kcmil, 1113 (37, 61)
-------------------------	--------------------------------------

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	470 mm
mm	
Dimension - Length Overall	18.51 in
inch	

General

Trade Name	HYSPLICE™
Die Index	727
UPC	781810085868
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810085868
UPC 14 Digit GTIN	00781810085868

Logistics

Minimum Pack Quantity	1
Pallet Quantity	432
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)