



YTS451A, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS451A](#)

Aluminum Full Tension HYSPLICE™, 1192.5-1272 Kcmil, 727 Index



Features

- ACSR Full Tension Compression Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	• 1192.5 (61) Kcmil • 1272 (61) Kcmil
-------------------------	---

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	467 mm
	mm
Dimension - Length Overall	18.40 in
	inch

General

Trade Name	HYSPLICE™
Die Index	727
UPC	781810125175
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810125175
UPC 14 Digit GTIN	00781810125175

Logistics

Minimum Pack Quantity	1
Pallet Quantity	480
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)