



YTS451AR, Aluminum Full Tension Splice

By Burndy
Catalog # [YTS451AR](#)



Al Tubing Full Tension Splice, 840.2, 853.7, 862.7, 927.2 kcmil
ACAR, 19.50" L, 725 Index

Features

- Aluminum Compression Full Tension Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACAR Str Size	840.2 Kcmil 853.7 Kcmil 862.7 Kcmil 927.2 Kcmil
---------------------------	---

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	497 mm
	mm
Dimension - Length Overall	19.58 in
	inch

General

Trade Name	HYSPLICE™
Die Index	725
UPC	781810016237
Prefilled Oxide Inhibitor	Y
Material	Aluminum
UPC 12 Digit	781810016237
UPC 14 Digit GTIN	00781810016237

Logistics

Minimum Pack Quantity	1
Pallet Quantity	600
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)