



YTS451R, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS451R](#)



Full Tension Two-piece Splice, Al Sleeve, 715.5kcmil-795kcmil
ACSR, 250 kV, 28.96" L, 725 Index

Features

- ACSR Full Tension Compression Splice
- 2-Piece

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance Status	CM
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	• 715.5 (54/7) Crow kcmil • 715.5 (24/7) Stilt kcmil • 715.5 (26/7) Starling kcmil • 715.5 (30/19) Redwing kcmil • 795 (54/7) Condor kcmil • 795 (26/7) Drake kcmil
Conductor - ACSR Str Size Range	715.5 (54/7) Crow kcmil-795 (26/7) Drake kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Package Height	0.000 in
Package Weight	0.000 lb.
Package Length	0.000 in
Package Width	0.000 in
Dimension - L Length Overall	735.6 mm
mm	
Dimension - Length Overall	28.96 in
inch	

General

Trade Name	HYSPLICE™
Die Index	725
UPC	781810016299
Material	Aluminum
UPC 12 Digit	781810016299
UPC 14 Digit GTIN	00781810016299

Logistics

Minimum Pack Quantity	1
Pallet Quantity	280
Carton Quantity	8

Product Assets

[Catalog \[English\]](#)