



YTS451R48RS, Full Tension Splice Kit for ACSR

By Burndy
Catalog # [YTS451R48RS](#)



Full Tension Splice Kit for ACSR Conductor

Features

- ACSR Full Tension Compression Splice Kit

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	UI
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - ACSR Str Size	• 715.5 (26/7) Starling kcmil • 715.5 (30/19) Redwing kcmil • 795 (54/7) Condor kcmil • 795 (26/7) Drake kcmil
Conductor - ACSR Str Size Range	715.5 (26/7) Starling kcmil-795 (26/7) Drake kcmil

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - Outside Diameter	1.80 in
Dimension - Length Overall	28.96 in

General

Trade Name	HYSPLICE™
UPC	781810507018
UPC 12 Digit	781810507018
UPC 14 Digit GTIN	00781810507018

Logistics

Minimum Pack Quantity	6
Pallet Quantity	210
Carton Quantity	6

Product Assets

[Catalog \[English\]](#)