



YTS451R48RSHT, ACSR - Full Tension Compression Splice

By Burndy
Catalog # [YTS451R48RSHT](#)

Compression High Temperature Splice



Features

- ACSR Full Tension Compression High Temperature Splice

Specifications

Certification - ETL	No
Certification - UL Recognized	No
Standards - RoHS Compliance	CM
Status	
Certification - cULus	No
UL Listed	No
Certification - CSA Approved	No

Conductor

Conductor - AL Str Size	12 AWG
Conductor - AL Str Size Range	12 AWG
Conductor - ACSR Str Size	6 (6/1) Turkey AWG
Conductor - ACSS Str Size	715.5 (26/7) kcmil
Conductor - ACSS Str Size Range	
Conductor - ACSS Str Size	715.5 (26/7) kcmil
Conductor - ACSR Str Size	6 (6/1) Turkey AWG
Conductor - ACSR Str Size Range	

Configuration

Connector Type	Splice
----------------	--------

Dimensions

Dimension - L Length Overall	914 mm
Dimension - B Length inch	4.19 in
Dimension - Outside Diameter inch	1.80 in
Dimension - Length Overall inch	36.00 in

General

Trade Name	HYSPLICE™
UPC	781810474662
UPC 12 Digit	781810474662
UPC 14 Digit GTIN	00781810474662

Logistics

Minimum Pack Quantity	1
Pallet Quantity	72
Carton Quantity	4

Product Assets

[Catalog \[English\]](#)